



Description: EPIC M-D 1.0 D-Sub stamped contacts-on-reel_

Lapp code: Lapp 44429013

The **Test voltage** of the cable Lapp 44429013 is /.

/

/

In our Cable list on next page you can find all interesting information acc. article Lapp 44429013 and much more.

CABLE LIST - all informations you need you can find here

| Product Name | Lapp Nr. | Article | Version | Conductor cross-section (mm ²) | Surface | Stripping length (mm) | Note | Pieces / PU |
|---|---------------|--|---------|--|-------------|-----------------------|----------------------------|-------------|
| Contacts | | | | | | | | |
| EPIC M-D 1.0 D-Sub stamped contacts-on-reel | Lapp 44429011 | EPIC® D-SUB SCBG AU G2 0,08-0,22 (500) | male | 0,08 - 0,22 | Au (0.8 µm) | 2.5 + 0.5 | 1 reel (PU) = 500 contacts | 1 |
| EPIC M-D 1.0 D-Sub stamped contacts-on-reel | Lapp 44429007 | EPIC® D-SUB BCBG AU G2 0,08-0,22 (500) | female | 0,08 - 0,22 | Au (0.8 µm) | 2.5 + 0.5 | 1 reel (PU) = 500 contacts | 1 |
| EPIC M-D 1.0 D-Sub stamped contacts-on-reel | Lapp 44429013 | EPIC® D-SUB SCBG AU G3 0,08-0,22 (500) | male | 0,08 - 0,22 | Au (0.1 µm) | 2.5 + 0.5 | 1 reel (PU) = 500 contacts | 1 |
| EPIC M-D 1.0 D-Sub stamped contacts-on-reel | Lapp 44429009 | EPIC® D-SUB BCBG AU G3 0,08-0,22 (500) | female | 0,08 - 0,22 | Au (0.1 µm) | 2.5 + 0.5 | 1 reel (PU) = 500 contacts | 1 |
| EPIC M-D 1.0 D-Sub stamped contacts-on-reel | Lapp 44429012 | EPIC® D-SUB SCBG AU G2 0,22-0,56 (500) | male | 0,22 - 0,56 | Au (0.8 µm) | 2.5 + 0.5 | 1 reel (PU) = 500 contacts | 1 |
| EPIC M-D 1.0 D-Sub stamped contacts-on-reel | Lapp 44429008 | EPIC® D-SUB BCBG AU G2 0,22-0,56 (500) | female | 0,22 - 0,56 | Au (0.8 µm) | 2.5 + 0.5 | 1 reel (PU) = 500 contacts | 1 |
| EPIC M-D 1.0 D-Sub stamped contacts-on-reel | Lapp 44429014 | EPIC® D-SUB SCBG AU G3 0,22-0,56 (500) | male | 0,22 - 0,56 | Au (0.1 µm) | 2.5 + 0.5 | 1 reel (PU) = 500 contacts | 1 |
| EPIC M-D 1.0 D-Sub stamped contacts-on-reel | Lapp 44429010 | EPIC® D-SUB BCBG AU G3 0,22-0,56 (500) | female | 0,22 - 0,56 | Au (0.1 µm) | 2.5 + 0.5 | 1 reel (PU) = 500 contacts | 1 |