



**Description:** ÖLFLEX CRANE VS (N)SHTÖU 4 G 25\_

**Lapp code:** Lapp 00440243

The **Test voltage** of the cable Lapp 00440243 is 3000 V.

## Application range

- For use in hoists, transport and conveyor systems
- Cables are reeled, unreeled, and guided by roller trains
- In dry or damp interiors, outdoors, or not more than 2 weeks without interruption in industrial water
- The application profiles for ÖLFLEX® CRANE and ÖLFLEX(R) LIFT cables can be found in the appendix, selection table A3
- The assembly and handling guidelines for ÖLFLEX® CRANE cables can be found in the catalogue appendix, technical table T4; for ÖLFLEX(R) LIFT cables please see the catalogue appendix, technical table T5

## Product Make-up

- Strands of tinned-copper wires
- Core insulation: rubber compound type 3GI3
- Central supporting element
- Support braid integrated in the outer sheath
- Outer sheath: rubber compound, type 5GM5

In our Cable list on next page you can find all interesting information acc. article Lapp 00440243 and much more.

CABLE LIST - all informations you need you can find here

Product Name	Lapp Nr.	Number of cores and mm <sup>2</sup> per conductor	Outer diameter (mm)	Tensile strength (N)	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® CRANE VS (N)SHTÖU						
ÖLFLEX CRANE VS (N)SHTÖU 7 G 1,5	Lapp 0044008	7 G 1,5	18.8	2000	100.8	430
ÖLFLEX CRANE VS (N)SHTÖU 12 G 1,5	Lapp 0044009	12 G 1,5	25.3	2000	172.8	820
ÖLFLEX CRANE VS (N)SHTÖU 18 G 1,5	Lapp 0044010	18 G 1,5	25.3	2000	259.2	930
ÖLFLEX CRANE VS (N)SHTÖU 24 G 1,5	Lapp 0044011	24 G 1,5	30.1	2000	345.6	1260
ÖLFLEX CRANE VS (N)SHTÖU 36 G 1,5	Lapp 0044036	36 G 1,5	34.0	2000	518.4	1650
ÖLFLEX CRANE VS (N)SHTÖU 7 G 2,5	Lapp 0044015	7 G 2,5	21.6	2000	168.0	630
ÖLFLEX CRANE VS (N)SHTÖU 12 G 2,5	Lapp 0044016	12 G 2,5	29.4	2000	288.0	1150
ÖLFLEX CRANE VS (N)SHTÖU 5 G 4	Lapp 00440333	5 G 4	19.6	2000	192.0	510
ÖLFLEX CRANE VS (N)SHTÖU 4 G 10	Lapp 00440223	4 G 10	23.4	2000	384.0	830
ÖLFLEX CRANE VS (N)SHTÖU 4 G 16	Lapp 00440233	4 G 16	25.5	2000	614.4	1170
ÖLFLEX CRANE VS (N)SHTÖU 5 G 16	Lapp 00440323	5 G 16	27.5	2400	768.0	1400
ÖLFLEX CRANE VS (N)SHTÖU 4 G 25	Lapp 00440243	4 G 25	32.6	3000	960.0	1850
ÖLFLEX CRANE VS (N)SHTÖU 4 G 35	Lapp 00440253	4 G 35	34.8	4000	1344.0	2250
ÖLFLEX CRANE VS (N)SHTÖU 4 G 50	Lapp 00440263	4 G 50	40.6	6000	1920.0	3200
ÖLFLEX CRANE VS (N)SHTÖU 4 G 70	Lapp 00440283	4 G 70	44.8	8000	2688.0	4200
ÖLFLEX CRANE VS (N)SHTÖU 4 G 95	Lapp 00440293	4 G 95	51.2	11000	3648.0	5550